


BEAKER FOR HIGH-PERFORMANCE MIXING

Powder dispersion made easy, foam-free mixing.


Developed using CFD and experimental testing, with an ergonomic design.


Key Features:

- Non-Vortex Design: Suppresses vortex formation to reduce foaming and air entrapment
- Efficient Mixing:
 CFD-optimized baffles enhance fluid circulation and usable mixing volume
- Safe and Lightweight:
 Durable polymer body shatterproof and easy to handle
- Chemical-Resistant PEN:
 Made from PEN for excellent resistance to solvents, acids, and heat
- Optional Lid:
 A dedicated sliding lid compatible with the non-vortex beaker allows impeller mixing while minimizing splashing and contamination



Vorticity Distribution from CFD Simulation:





Applications:

Viscous liquids:

- Latex emulsions, paints& coatings
- · Creams & lotions
- · Polymer solutions

Powder-liquid:

- · Pigments dispersion
- · Pharmaceutical
- · Suspensions
- · Ceramic slurries

Degassing-sensitive:

- · Cell culture media
- · Specialty chemicals
- · Sensitive to entrapped air

Compliance & Sterilization:

Biocompatibility:

· USP <88> Class VI

· USP <87>

· ISO 10993-4, -10

· FDA 21 CFR

Chemical Safety:

· RoHS 2 compliant

· REACH compliant

· PFAS-free

Sterilization Methods:

· Gamma

· Autoclave

· EtO

Specifications:




P/N	Volume (mL)	Weight (g) (Without lid)	Dimension (mm) (Φ x H x Wall thickness)	Baffle width (mm)
CL500	500	62 ± 2.0	87 x 113 x 1.0	17
CL750	750	71 ± 2.0	100 x 130 x 1.2	20
CL1000	1000	101 ± 3.0	109 x 143 x 1.3	22
CL2000	2000	189 ± 6.0	139 x 180 x 1.6	28

Recommended Geometric Proportions for Baffled Beaker Mixing:

Impeller Diameter / Baffled Beaker Diameter : 0.3 - 0.5

Liquid Height / Baffled Beaker Diameter : 1.0

Impeller Clearance (from beaker bottom) / Baffled Beaker Diameter: 0.3 – 0.5



1 & 2F, No. 11-1, Wuquan 1st Road, Xinzhuang District, New Taipei City 24892, Taiwan

t +886-2-22901122 f +886-2-22995222

盈豐材料股份有限公司

@

www https://www.flxr.engineering

@ hello@flxr.engineering

24892新北市新莊區五權一路11-1號1、2樓





